
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB500-266

NB500-266

Beclin 1 Antibody



Unit Size
0.1 ml

Concentration
This product is unpurified. The exact concentration of antibody is not quantifiable.

Storage
Store at 4C. Do not freeze.

Applications
WB

Species
Human, Mouse

Molecular Weight
52kDa

Host
Rabbit

Clonality
Polyclonal

Purity
Whole antisera

Preservative
0.1% Sodium Azide


Updated 3/9/2013 2.0

Immunogen
Full length human Beclin 1 protein [Swiss-Prot# Q14457]

Recommended Dilutions
Western Blot 1:500

Uses
This Beclin 1 antibody is useful for Western blot, where a band is observed at ~52 kDa representing Beclin 1. There is also a higher MW non-specific band at ~66 kDa.

Images
Western Blot: Beclin 1 Antibody [NB500-266] - Detection of Beclin 1 in liver lysates using NB 500-266. Lane 1: mouse liver Lane 2: human liver



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com