
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB600-532H

NB600-532H

Beta Actin Antibody [HRP]



Unit Size
0.1 mg

Concentration
1.0 mg/ml

Storage
Store at 4C in the dark.

Applications
WB, IP

Species
Human, Mouse

Host
Rabbit

Clonality
Polyclonal

Conjugate
HRP

Purity
Immunogen affinity purified

Preservative
No Preservative

Updated 3/9/2013 2.0

Specificity/Sensitivity
Detects a single clean band at 40kD representing actin.

Immunogen
The epitope recognized by this antibody maps to the N-terminus of human Beta-actin using the numbering given in Swiss-Prot entry P60709 (GeneID 60).

Recommended Dilutions
Immunoprecipitation 2-5 ug/mg, Western Blot 1:5000-1:15000

Buffer
PBS

Uses
This antibody can be used in WB where a 40 kDa band is detected in HeLa whole cell lysate and mouse NIH3T3 cells. Optimal dilutions shoudl be determined by the end user.

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB600-532H

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com