
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB120-11884

NB120-11884

C5AR1 Antibody (W17/1)



Unit Size
0.05 mg

Concentration
0.1 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
FLOW, IHC, IHC-Fr, IHC-P, IP

Species
Human

Host
Mouse

Clonality
Monoclonal

Isotype
IgG1

Purity
Protein G purified

Preservative
0.02% Sodium Azide

Updated 3/9/2013 2.0

Specificity/Sensitivity
C5R1 (W17/1)

Immunogen
Unfortunately, this information is considered to be commercially sensitive, (extracellular domain of the N-terminus).

Recommended Dilutions
Flow Cytometry, Immunoprecipitation (-), Immunohistochemistry-Frozen, Immunohistochemistry-Paraffin, Immunohistochemistry

Buffer
PBS, 0.1% BSA

Uses
Not suitable for IP. Suggested starting working dilution 1/10.

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB120-11884

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com