
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB110-81601G

NB110-81601G

TRPM2 Antibody [DyLight 488]



Unit Size
0.1 ml

Concentration
1.25 mg/ml

Storage
Store at 4C in the dark.

Applications
WB, IHC

Species
Mouse, Rat

Host
Rabbit

Clonality
Polyclonal

Conjugate
DyLight 488

Purity
Peptide affinity purified

Preservative
No Preservative

Updated 3/9/2013 2.0

Specificity/Sensitivity
This is specific for isoform 1, or the long isoform (TRPM2-L), of TRPM2.

Immunogen
Synthetic peptide made to a C-terminal portion of the rat protein (within residues 1430-1508). [Swiss-Prot# Q5G856]

Recommended Dilutions
immunohistochemistry 1:200, Western Blot 1:500-1:1000,

Buffer
50mM sodium borate

Uses
This antibody is useful for Western blot, where a band is seen ~181 kDa. This antibody is also useful for immunohistochemistry.

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB110-81601G

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com