
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB110-95574

NB110-95574

CYLD Antibody



Unit Size
0.1 ml

Concentration
1 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
WB

Species
Human, Mouse, Bovine, Primate, Rat (Negative)

Molecular Weight
120kDa

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.1% Sodium Azide

Updated 3/9/2013 2.0

Immunogen
Synthetic peptide made to an internal portion of human CYLD (within residues 500-600). [Swiss-Prot# Q9NQC7]

Recommended Dilutions
Western Blot 2.0 mg/ml

Buffer
Tris-citrate/phosphate, pH 7-8

Uses
This CYLD antibody is useful for Western blot, where a doublet is seen ~120 kDa (Hellerbrand, et al.)

Images
Detection of CYLD in Jurkat whole cell extract using NB110-95574.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com