
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB110-59723

## NB110-59723

# EGR2 Antibody



### Unit Size
0.1 ml

### Concentration
0.9 mg/ml

### Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

### Applications
WB

### Species
Human, Porcine

### Molecular Weight
50kDa

### Host
Rabbit

### Clonality
Polyclonal

### Purity
Immunogen affinity purified

### Preservative
0.1% Sodium Azide

Updated 3/9/2013 2.0


### Immunogen
A synthetic peptide made to a portion of human EGR2 (within residues 200-300). [Swiss-Prot# P11161]

### Recommended Dilutions
Western Blot 2 ug/ml

### Buffer
Tris-glycine, 150 mM NaCl

### Uses
This EGR2 antibody is useful for Western blot where a band is seen at ~50 kDa. There is also a strong non-specific band at ~75 kDa.

### Images
Western Blot: EGR2 Antibody [NB110-59723] - Detection of EGR2 in human fetal lung tissue using NB110-59723.




*Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months.* ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

**Novus USA**
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

**Novus Canada**
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

**Novus Europe**
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com