
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB110-60982R

NB110-60982R

Beclin 2 Antibody [DyLight 550]



Unit Size
0.1 ml

Concentration
0.9 mg/ml

Storage
Store at 4C in the dark.

Applications
WB

Species
Human

Host
Rabbit

Clonality
Polyclonal

Conjugate
DyLight 550

Purity
Peptide affinity purified

Preservative
No Preservative

Updated 3/9/2013 2.0

Specificity/Sensitivity
Beclin 2

Immunogen
A synthetic peptide made to an N-terminal region (within residues 1-100) of the human beclin 2 protein. [NCBI# XP_945075]

Recommended Dilutions
Western Blot 1:200-1:500

Buffer
50mM sodium borate

Uses
This antibody is useful for Western blot analysis, where a band is seen at ~50 kDa.

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB110-60982R

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com