
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB110-17098

NB110-17098

Clostridium Botulinum Toxin A Antibody



Unit Size
0.2 mg

Concentration
1.6 mg/ml

Storage
Aliquot and store at -20C or -80C. Avoid freeze-thaw cycles.

Applications
WB, DB, ELISA

Species
Bacteria

Host
Rabbit

Clonality
Polyclonal

Purity
Protein G purified

Preservative
No Preservative

Updated 3/9/2013 2.0

Specificity/Sensitivity
Clostridium botulinum Type A Neurotoxin.

Immunogen
Type A Neurotoxin (C. botulinum)

Recommended Dilutions
Dot Blot
ELISA 1:10000
Western Blot

Buffer
PBS [pH 7.2] containing 20% glycerol

Uses
Predicted molecular weight: 149 kDa.

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB110-17098

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com