Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB110-40593

NB110-40593

SUPT5H Antibody

Unit Size
0.1 mg

Concentration
1.0 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
WB, IHC-P, IP (-)

Species
Human

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.09% Sodium Azide

Updated 3/9/2013 2.0


Immunogen
The immunogen recognized by this antibody maps to a region between residue 1040 and the C-terminus (residue 1087) of human Suppressor of Ty 5 Homolog using the numbering given in entry NP_003160.2 (GeneID 6829).

Recommended Dilutions
Immunoprecipitation (Negative), Western Blot 1:2000 -1:10000, Immunohistochemistry-Paraffin

Buffer
Tris-citrate/phosphate buffer, pH 7 to 8

Uses
This antibody is useful for Western Blot Not recommended for Immunoprecipitation, use NB110-40592.

Images (more available at www.novusbio.com/NB110-40593)



Western Blot: SUPT5H Antibody [NB110-40593] - Detection of Human SUPT5H on HeLa whole cell lysate using NB110-40593. SUPT5H was immunoprecipitated by rabbit anti-SUPT5H antibody NB110-40592.



Immunohistochemistry-Paraffin: SUPT5H Antibody [NB110-40593] - FFPE section of mouse teratoma. Affinity purified rabbit anti-SUPT5H used at a dilution of 1:250.

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com