
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB110-40764C

NB110-40764C

TIP47 Antibody [DyLight 650]



Unit Size
0.1 ml

Concentration
0.93 mg/ml

Storage
Store at 4C in the dark.

Applications
WB

Species
Human, Primate, Porcine

Host
Rabbit

Clonality
Polyclonal

Conjugate
DyLight 650

Purity
Peptide affinity purified

Preservative
No Preservative

Updated 3/9/2013 2.0

Specificity/Sensitivity
TIP47

Immunogen
A synthetic peptide made to a region within the C-terminus (within residues 350-435) of the human TIP47 protein. [Swiss-Prot# O60664]

Recommended Dilutions
Western Blot 2 ug/ml

Buffer
50mM sodium borate

Uses
This antibody is useful for Western blot analysis where a band is seen at ~47 kDa, representing isoform B in both human (faint) and mouse lysates. In some samples, a ~28 kDa band may be observed which represents a splice isoform.

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB110-40764C

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com