
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-80829

## NB100-80829

# STEAP2 Antibody



## Unit Size
0.05 mg

## Concentration
Concentrations vary lot to lot. See vial label for concentration.

## Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

## Applications
WB, IHC, IHC-P

## Species
Human, Mouse

## Host
Rabbit

## Clonality
Polyclonal

## Isotype
IgG

## Purity
Immunogen affinity purified

## Preservative
0.02% Sodium Azide

Updated 3/9/2013 2.0

## Immunogen
Synthetic peptide; a 16 amino acid peptide from near the carboxy terminus of human STEAP2 protein.

## Recommended Dilutions
Immunohistochemistry, Immunohistochemistry-Paraffin 10 ug/ml, Western Blot 1 ug/ml

## Buffer
PBS

## Uses
For IHC-Paraffin, use heat induced antigen retrieval in pH 6.0 citrate buffer.

## Images
Immunohistochemistry-Paraffin: STEAP2 Antibody [NB100-80829] - Staining of human skin. Immunohistochemistry of formalin-fixed, paraffin-embedded tissue after heat-induced antigen retrieval. Antibody concentration 10 ug/ml.



*Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months.* ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

**Novus USA**
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

**Novus Canada**
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

**Novus Europe**
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com