
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-77867

NB100-77867

TWEAK Antibody (CARL-1)



Unit Size
0.1 mg

Concentration
0.5 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
ELISA, FLOW

Species
Human

Host
Mouse

Clonality
Monoclonal

Isotype
IgG3 Kappa

Purity
Affinity purified

Preservative
0.09% Sodium Azide

Updated 3/9/2013 2.0


Immunogen
hTWEAK/2PK-3 transfectant cells

Recommended Dilutions
ELISA 1-4 ug/ml
Flow Cytometry

Buffer
PBS, pH 7.2

Uses
IHC and Neutralization use reported in literature.

Images
Human TWEAK transfected cells stained with Carl-1 PE



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com