
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-60426

## NB100-60426

# RBM27 Antibody



## Unit Size
0.1 mg

## Concentration
0.2 mg/ml

## Storage
Store at 4C. Do not freeze.

## Applications
WB, IHC, IHC-P, IM, IP

## Species
Human

## Host
Rabbit

## Clonality
Polyclonal

## Purity
Immunogen affinity purified

## Preservative
0.09% Sodium Azide

Updated 3/9/2013 2.0


## Immunogen
The immunogen recognized by this antibody maps to a region between residue 700 and 750 of human RNA binding motif protein 27 using the numbering given in entry Q9P2N5.2 (GeneID 54439).

## Recommended Dilutions
Immunohistochemistry, Immunohistochemistry-Paraffin 1:100 - 1:500, Immunoprecipitation 2 to 5 ug/mg lysate, Western Blot 1:2000 to 1:10000, Immunomicroscopy

## Buffer
Tris-citrate/phosphate buffer, pH 7 to 8

## Uses
Western Blot and Immunoprecipitation

## Images (more available at www.novusbio.com/NB100-60426)



Western Blot: RBM27 Antibody [NB100-60426] - Detection of Human RBM27 on HeLa whole cell lysate using NB100-60426. RBM27 was also immunoprecipitated by rabbit anti-RBM27 antibody NB100-60427.



Immunohistochemistry-Paraffin: RBM27 Antibody [NB100-60426] - Detection of Human RBM27 by Immunohistochemistry. Sample: FFPE section of human breast carcinoma. Antibody: Affinity purified rabbit anti-RBM27 used at a dilution of 1:250. Detect... See more at www.novusbio.com/NB100-60426

*Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months.* ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

**Novus USA**
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

**Novus Canada**
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

**Novus Europe**
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com