
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-2523

# NB100-2523

# SIRT6 Antibody



## Unit Size
0.1 ml

## Concentration
1 mg/ml

## Storage
Store at 4C. Do not freeze.

## Applications
WB

## Species
Human

## Molecular Weight
39kDa

## Host
Rabbit

## Clonality
Polyclonal

## Purity
Immunogen affinity purified

## Preservative
0.1% Sodium Azide

Updated 3/9/2013 2.0


## Immunogen
A synthetic peptide made to an internal region of the human SIRT6 protein (within residues 250-350). [Swiss-Prot Q8N6T7]

## Recommended Dilutions
Western Blot 0.5-2.0 ug/ml

## Buffer
Tris-citrate/phosphate, pH 7-8

## Uses
This SIRT6 antibody is useful for Western blot analysis, where a band is seen at ~39 kDa. A higher MW band ~59 kDa may be seen with lower dilutions (ie: 2 ug/ml).

## Images
Western Blot: SIRT6 Antibody [NB100-2523] - Detection of SIRT6 in HeLa whole cell lysate.




*Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months.* ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

**Novus USA**
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

**Novus Canada**
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

**Novus Europe**
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com