
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-2596

NB100-2596

TIF1 alpha Antibody



Unit Size
0.1 ml

Concentration
0.2 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
WB, IHC, IHC-P, IP, PLA

Species
Human, Mouse

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.09% Sodium Azide

Updated 3/9/2013 2.0

Immunogen
The immunogen recognized by this antibody maps to a region between residue 700 and 750 of human Transcriptional Intermediary Factor 1 Alpha (Tripartite Motif-Containing 24) using the numbering given in entry NP_056989.2 (GeneID 8805).

Recommended Dilutions
Immunohistochemistry 1:250
Immunohistochemistry-Paraffin 1:250
Immunoprecipitation 2 -5 ug/mg lysate
Proximity Ligation Assay
Western Blot 1:2000 -1:10000


Buffer
Tris-buffered Saline and 0.1% BSA

Uses
This antibody is useful for Western Blot and Immunoprecipitation

References
Allton K, Jain AK, Herz H-M, et al. From the Cover: Trim24 targets endogenous p53 for degradation. PNAS ;106(28):11612-11616. 2009. [PMID: 19556538

Images (more available at www.novusbio.com/NB100-2596)

Western Blot: TIF1 alpha Antibody [NB100-2596] - Detection of Human and Mouse TIF1 alpha/TRIM24 on HeLa whole cell lysate using NB100-2596. TIF1 alpha/TRIM24 was also immunoprecipitated by rabbit anti-TIF1 alpha/TRIM24 antibody NB100-2597.



Immunohistochemistry-Paraffin: TIF1 alpha Antibody [NB100-2596] - FFPE section of mouse squamous cell carcinoma. Antibody used at a dilution of 1:250.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com