
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-598R

NB100-598R

BRCA1 Antibody (RAY) [DyLight 550]



Unit Size
0.1 ml

Concentration
2.76 mg/ml

Storage
Store at 4C in the dark.

Applications
WB, ICC/IF, IP

Species
Human

Host
Mouse

Clonality
Monoclonal

Conjugate
DyLight 550

Purity
Protein G purified

Preservative
No Preservative

Updated 3/9/2013 2.0

Specificity/Sensitivity
This recognizes the epitope aa 1314-1600.

Immunogen
Human BRCA1 (between residues 1314-1864).

Recommended Dilutions
immunofluorescence, immunoprecipitation, Western Blot 2-4 ug/ml

Buffer
50mM sodium borate

Uses
A band can be seen ~220-240 kDa in Western blot. The investigator should determine the optimal working dilution for a specific application.

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB100-598R

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com