
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-359C

## NB100-359C

# ATRIP Antibody [DyLight 650]



### Unit Size
0.1 ml

### Concentration
1.0 mg/ml

### Storage
Store at 4C in the dark.

### Applications
WB, IP

### Species
Human

### Host
Rabbit

### Clonality
Polyclonal

### Conjugate
DyLight 650

### Purity
Protein G purified

### Preservative
No Preservative

Updated 3/9/2013 2.0

### Immunogen
A synthetic peptide derived from a sequence between amino acids 500-550 of the human ATRIP protein (aka TREX1) [Gene ID 11277].

### Recommended Dilutions
immunoprecipitation 3-8 ug/ml
Western Blot 1:5000-1:15000

### Buffer
50mM sodium borate

### Uses
This antibody may be used for Western blot and immunoprecipitation. Immunohisto/cytochemistry have not been tested using this antibody.

### Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB100-359C

*Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months.* ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

**Novus USA**
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

**Novus Canada**
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

**Novus Europe**
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com