
NB100-399

Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-399

NB100-399

Menin Antibody



Unit Size
0.1 ml

Concentration
1.0 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
WB, IP

Species
Human

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.1% Sodium Azide

Updated 3/9/2013 2.0


Immunogen
A synthetic peptide, which represented a portion of human Multiple Endocrine Neoplasia 1 encoded within exon 11 (MEN1 LocusLink ID 4221).

Recommended Dilutions
Immunoprecipitation 2 -10 ug/mg of lysate, Western Blot 1:500 - 1:5000

Buffer
Tris-citrate/phosphate buffer, pH 7 to 8

Uses
This antibody may be used for Western Blot, where a doublet band should be seen at ~72 kDa. Suggested working dilutions: * Western Blot - 1:500-1:5,000 Immunoprecipitation - 2 to 10 ug/mg lysate Immunofluorescence - ND *The investigator should determine the optimal working dilution for a specific application.

Images



Western Blot: Menin Antibody [NB100-399] - A. Whole cell lysate (40 mcg - E; 10 mcg - T) from 293T cells untreated (E) or transfected with a Menin expression construct (T). B. Whole cell lysate from one 10 cm plate of untreated 293T cells. A... See more at www.novusbio.com/NB100-399

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com