9F, No. 108, Jhouzih St.,Taipei, Taiwan
Tel: + 886-2-8751-1888 Fax: + 886-2-6602-1218
E-mail: sales@abnova.com

Datasheet

RSL1D1 polyclonal antibody

Catalog Number: PAB18755

Regulation Status: For research use only (RUO)

Product Description: Goat polyclonal antibody raised against synthetic peptide of RSL1D1.

Immunogen: A synthetic peptide corresponding to amino acids at internal region of human RSL1D1.

Sequence: C-PTARKQLDKEQVRK

Host: Goat

Theoretical MW (kDa): 75

Reactivity: Human

Applications: ELISA, WB-Ce
(See our web site product page for detailed applications information)

Protocols: See our web site at http://www.abnova.com/support/protocols.asp or product page for detailed protocols

Form: Liquid

Purification: Antigen affinity purification

Concentration: 0.5 mg/mL

Recommend Usage: ELISA (1:16000)
Western Blot (0.3-1 ug/mL)
The optimal working dilution should be determined by the end user.

Storage Buffer: In Tris saline, pH 7.3 (0.02% sodium azide, 0.5% BSA)

Storage Instruction: Store at -20°C.
Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 26156

Gene Symbol: RSL1D1

Gene Alias: CSIG, DKFZP564M182, L12, MGC138433, MGC142259, PBK1