9F, No. 108, Jhouzih St.,Taipei, Taiwan
Tel: + 886-2-8751-1888 Fax: + 886-2-6602-1218
E-mail: sales@abnova.com

Datasheet

PGLYRP1 purified MaxPab mouse polyclonal antibody (B03P)

Catalog Number: H00008993-B03P

Regulation Status: For research use only (RUO)

Product Description: Mouse polyclonal antibody raised against a full-length human PGLYRP1 protein.

Immunogen: PGLYRP1 (NP_005082.1, 1 a.a. ~ 196 a.a) full-length human protein.

Sequence:
MSRRSMLLAWALPSLLRLGAAQETEDPACCSPIVPRN
EWKALASECAQHLSLPLRYVVVSHTAGSSCNTPASCQ
QQARNVQHYHMKTLGWCDVGYNFLIGEDGLVYEGRG
WNFTGAHSGHLWNPMSIGISFMGNYMDRVPTPQAIR
AAQGLLACGVAQGALRSNYVLKGHRDVQRTLSPGNQ
LYHLIQNWPHYRSP

Host: Mouse

Reactivity: Human

Applications: Det Ab, WB-Tr
(See our web site product page for detailed applications information)

Protocols: See our web site at http://www.abnova.com/support/protocols.asp or product page for detailed protocols

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 8993

Gene Symbol: PGLYRP1

Gene Alias: MGC126894, MGC126896, PGLYRP, PGRP, PGRP-S, PGRPS, TAG7, TNFSF3L