9F, No. 108, Jhouzih St.,Taipei, Taiwan
Tel: + 886-2-8751-1888 Fax: + 886-2-6602-1218
E-mail: sales@abnova.com

Datasheet

TRDN polyclonal antibody

Catalog Number: PAB23499

Regulation Status: For research use only (RUO)

Product Description: Rabbit polyclonal antibody raised against recombinant TRDN.

Immunogen: Recombinant protein corresponding to amino acids of human TRDN.

Sequence:
VSTRKESLQLHNVTKAEKPARVSKDVEDVPASKKAKE
GTEDVSPTKQKSPISFFQCVYLDGYNGYGFQFP

Host: Rabbit

Reactivity: Human

Applications: IHC-P
(See our web site product page for detailed applications information)

Protocols: See our web site at http://www.abnova.com/support/protocols.asp or product page for detailed protocols

Form: Liquid

Purification: Antigen affinity purification

Isotype: IgG

Recommend Usage: Immunohistochemistry (1:200-1:500)
Western Blot (1:250-1:500)
The optimal working dilution should be determined by the end user.

Storage Buffer: In PBS, pH 7.5 (40% glycerol, 0.02% sodium azide)

Storage Instruction: Store at 4°C. For long term storage store at -20°C.
Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 10345

Gene Symbol: TRDN

Gene Alias: DKFZp779I2253, MGC88285, TDN, TRISK, TRISK51