
Europium Chelate W-1024 conjugated to Goat anti-Human IgG

Product Number	D17-110-20, D17-110-50, D17-110-1MG
Amount	20 μg, 50 μg, 1 mg
Concentration	≈ 1mg/mL
Store at	2-8°C
EU/Ab	5-9 per Ab



Form/Shipping & Storage
Supplied as liquid. Upon receipt, store at 2-8 °C. DO NOT FREEZE.

Handling
We recommend that the investigator determine the appropriate working concentration for their specific application.Avoid exposure to heat and light.

Buffer
The product is in 50 mM Tris (pH 7.8) + 0.9% NaCl + 0.05% NaN_3.

Stability
Product should be stored at 2-8°C in the dark and be used within 6 months.

Note
For research use only, not for diagnostic or therapeutic use.

Spectral Characteristics

Visible absorption maxima	340
Emission maximum	615