ProSci

prosci-inc.com

HIGH PERFORMANCE ANTIBODIES ... AND MORE


ProSci Incorporated
12170 Flint Place
Poway, CA 92064

Toll Free: +1 (888) 513 9525
Local: +1 (858) 513 2638
Fax: +1 (858) 513 2692

techsupport@prosci-inc.com

MYH9 Antibody [2B3]

CATALOG NUMBER: 70-032



Immunohistochemistry of human breast tissue stained using MYH9 Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IF, IHC, WB
APPLICATIONS:	MYH9 antibody can be used in Western Blot starting at 1 - 3 ug/mL, and immunohistochemistry starting at 5 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Recombinant protein
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
STORAGE CONDITIONS:	MYH9 antibody can be stored short term 4 ˚C. For long term storage aliquot and store at -20 ˚C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2b,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	MYH9, BDPLT6, FTNS, MHA, Myosin heavy chain 9, NMMHC-IIA, NMMHC-A, Myosin-9, NMMHC II-a, DFNA17, EPSTS, NMHC-II-A, NMMHCA
ACCESSION NO.:	P35579
PROTEIN GI NO.:	6166599
OFFICIAL SYMBOL:	MYH9
GENE ID:	4627

Background

FOR RESEARCH USE ONLY

December 13, 2016