spectrum™
chemicals & laboratory products

Item Number	A1120
Item	Ammonium Acetate, Crystal, Reagent, ACS
CAS Number	631-61-8
Molecular Formula	$C_2H_7NO_2$
Molecular Weight	77.08

Assay	Min. 97%
pH of a 5% Solution @ 25°C	6.7-7.3
MAXIMUM LIMITS	
Insoluble Matter	0.005%
Residue after Ignition	0.01%
Chloride (Cl)	5 ppm
Nitrate (NO_3)	0.001%
Sulfate (SO_4)	0.001%
Heavy Metals (as Pb)	5 ppm
Iron (Fe)	5 ppm

Spectrum Chemicals & Laboratory Products

Corporate Headquarters:
14422 S. San Pedro St.
Gardena, CA 90248

East Coast Facility:
755 Jersey Ave.
New Brunswick, NJ 08901

(800) 813-1514 • (310) 516-8000 • Fax (310) 516-9843