spectrum™
chemicals & laboratory products

Item Number	B1261
Item	Oxybenzone, USP
CAS Number	131-57-7
Molecular Formula	$C_{14}H_{12}O_3$
Molecular Weight	228.24

Assay (Dried Basis)..... 97.0-103.0%
Congealing Temperature..... Min. 62°C

MAXIMUM LIMITS

Loss on Drying.....2.0%
Residual solvents..... To pass test

Spectrum Chemicals & Laboratory Products

Corporate Headquarters:
14422 S. San Pedro St.
Gardena, CA 90248

East Coast Facility:
755 Jersey Ave.
New Brunswick, NJ 08901

(800) 813-1514 • (310) 516-8000 • Fax (310) 516-9843