spectrum™
chemicals & laboratory products

Item Number	BE130
Item	Benzocaine, USP
CAS Number	94-09-7
Molecular Formula	$C_9H_{11}NO_2$
Molecular Weight	165.19

Assay (Dried Basis)	98.0-102.0%
Melting Range (Max. 2°C)	88°-92°C
Reaction	To pass test

MAXIMUM LIMITS

Loss on Drying	1.0%
Readily Carbonizable Substances	To pass test
Residue on Ignition	0.1%
Chloride	To pass test
Heavy Metals	0.001%
Ordinary Impurities	1%
Residual Solvents	To pass test

Spectrum Chemicals & Laboratory Products

Corporate Headquarters:
14422 S. San Pedro St.
Gardena, CA 90248

East Coast Facility:
755 Jersey Ave.
New Brunswick, NJ 08901

(800) 813-1514 • (310) 516-8000 • Fax (310) 516-9843