Item Number HY122

Item Hypromellose, Substitution Type 2910, USP

CAS Number 9004-65-3

Molecular Formula

Molecular Weight

Viscosity of a 2% Aqueous Solution @ 20°C	40-60 mPa·s
Assay:	
|Methoxy Groups	28.0-30.0%
|Hydroxypropoxy Groups	7.0-12.0%
pH	5.0-8.0
MAXIMUM LIMITS	
Loss on Drying	5.0%
Residue on Ignition	1.5%
Heavy Metals	20 ppm
Residual Solvents	To pass test

Spectrum Chemicals & Laboratory Products

Corporate Headquarters:
14422 S. San Pedro St.
Gardena, CA 90248

East Coast Facility:
755 Jersey Ave.
New Brunswick, NJ 08901

(800) 813-1514 • (310) 516-8000 • Fax (310) 516-9843