spectrum™
chemicals & laboratory products

Item Number	M1020
Item	Magnesium Acetate, Tetrahydrate, Crystal,
CAS Number	16674-78-5
Molecular Formula	(CH3COO)2Mg•4H2O
Molecular Weight	214.46

Assay [$(CH_3COO)_2Mg•4H_2O$]	98.0-102.0%
MAXIMUM LIMITS	
Insoluble Matter	0.005%
Sulfate (SO_4)	0.005%
Barium (Ba)	0.001%
Chloride (Cl)	0.001%
Iron (Fe)	5 ppm
Calcium (Ca)	0.01%
Manganese (Mn)	0.001%
Potassium (K)	0.005%
Sodium (Na)	0.005%
Strontium (Sr)	0.005%
Heavy Metals (as Pb)	5 ppm

Spectrum Chemicals & Laboratory Products

Corporate Headquarters:
14422 S. San Pedro St.
Gardena, CA 90248

East Coast Facility:
755 Jersey Ave.
New Brunswick, NJ 08901

(800) 813-1514 • (310) 516-8000 • Fax (310) 516-9843