spectrum™
chemicals & laboratory products

Item Number	ME111
Item	DL-Menthol, Crystal, USP
CAS Number	89-78-1
Molecular Formula	$C_{10}H_{20}O$
Molecular Weight	156.27

Congealing Range (A)	27°-28°C
Congealing Range (B)	30.5°-32.0°C
Specific Rotation, [α]D25	-2° to +2°
Chromatographic Purity	Min. 97%

MAXIMUM LIMITS

Nonvolatile Residue	0.05%
Readily Oxidizable Substances	To pass test
Residual solvents	To pass test

Spectrum Chemicals & Laboratory Products

Corporate Headquarters:
14422 S. San Pedro St.
Gardena, CA 90248

East Coast Facility:
755 Jersey Ave.
New Brunswick, NJ 08901

(800) 813-1514 • (310) 516-8000 • Fax (310) 516-9843