spectrum™
chemicals & laboratory products

Item Number	S1264
Item	Sodium Cyclamate
CAS Number	139-05-9
Molecular Formula	$C_6H_{12}NNaO_3S$
Molecular Weight	201.21

Assay (Dried Basis)	98.0-101.0%
Appearance of a 13% Solution in Water	Clear, practically colorless
pH of a 13% Solution	5.5-7.5
MAXIMUM LIMITS	
Loss on Drying	1.0%
Sulfate	To pass test
Arsenic (as As)	3 ppm
Selenium (Se)	0.003%
Cyclohexylamine	0.001%
Dicyclohexylamine	0.001%
Heavy Metals (as Pb)	0.001%
Extraneous Material	6 ppm

Spectrum Chemicals & Laboratory Products

Corporate Headquarters:
14422 S. San Pedro St.
Gardena, CA 90248

East Coast Facility:
755 Jersey Ave.
New Brunswick, NJ 08901

(800) 813-1514 • (310) 516-8000 • Fax (310) 516-9843