

**NBP1-19097****Bcr Antibody****Unit Size**

0.1 ml

**Concentration**

1.0 mg/ml

**Storage**

Store at 4C. Do not freeze.

**Applications**

WB, FLOW, ICC/IF, IHC, IHC-P, IP

**Species**

Human

**Host**

Rabbit

**Clonality**

Polyclonal

**Purity**

Immunogen affinity purified

**Preservative**

0.09% Sodium Azide

**Immunogen**

The immunogen recognized by this antibody maps to a region between residue 50 and 100 of human breakpoint cluster region using the numbering given in entry NP\_004318.3 (GeneID 613).

**Recommended Dilutions**


Flow Cytometry 0.25 mcg per 1X10<sup>6</sup> cells in 150 µl volume, Immunocytochemistry/Immunofluorescence, Immunohistochemistry, Immunohistochemistry-Paraffin 1:100-1:500, Immunoprecipitation 10 mcg/mg lysate, Western Blot

**Buffer**


Tris-citrate/phosphate buffer, pH 7 to 8

**Images (more available at [www.novusbio.com/NBP1-19097](http://www.novusbio.com/NBP1-19097))**

Western Blot: Bcr Antibody [NBP1-19097] - Whole cell lysate (1 mg for IP, 20% of IP loaded) from HeLa cells. Affinity purified rabbit anti-BCR antibody used for IP at 10 mcg/mg lysate. BCR was also immunoprecipitated by rabbit anti-BCR ant... See more at [www.novusbio.com/NBP1-19097](http://www.novusbio.com/NBP1-19097)



Immunocytochemistry/Immunofluorescence: Bcr Antibody [NBP1-19097] - Human K562 cells (contains the chromosomal translocation, t(9;22) that creates the BCR/ABL fusion gene). Antibody used at a dilution of 1:1,000 (1 µg/ml). Detection: Green-f... See more at [www.novusbio.com/NBP1-19097](http://www.novusbio.com/NBP1-19097)



Updated 3/9/2013 2.0

**Limitations:** This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit [www.novusbio.com/guarantee](http://www.novusbio.com/guarantee).**

**Novus USA**

8100 Southpark Way, A-8  
 Littleton, CO 80120  
 p) 888-506-6887  
 p) 303-730-1950  
 f) 303-730-1966  
[novus@novusbio.com](mailto:novus@novusbio.com)

**Novus Canada**

461 North Service Road West,  
 Unit B37  
 Oakville, ON L6M 2V5  
 p) 855-668-8722  
 f) 905-827-6402  
[canada@novusbio.com](mailto:canada@novusbio.com)

**Novus Europe**

12 Cambridge Science Park  
 Cambridge, UK CB4 0FQ  
 UK: p) +44-1223-426-001, f) +44-871-971-1635  
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79  
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340  
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31  
[europe@novusbio.com](mailto:europe@novusbio.com)

