

**NB100-58798****SPEN Antibody****Unit Size**

0.1 mg

**Concentration**

1.0 mg/ml

**Storage**

Store at 4C. Do not freeze.

**Applications**

WB, IP

**Species**

Human

**Host**

Rabbit

**Clonality**

Polyclonal

**Purity**

Immunogen affinity purified

**Preservative**

0.09% Sodium Azide

**Immunogen**

The immunogen recognized by this antibody maps to a region between residue 1350 and 1400 of human SMART/HDAC1 associated repressor protein (spen homolog, transcriptional regulator) using the numbering given in entry NP\_055816.2 (GeneID 23013).

**Recommended Dilutions**

Immunoprecipitation 2-5 ug/mg lysate, Western Blot

**Buffer**


Tris-citrate/phosphate buffer, pH 7 to 8

**Uses**

Western Blot - Not recommended for crude preparations. It can be used successfully for WB of enriched preparations (e.g. immunoprecipitated) SHARP.

**Images**

Western Blot: SPEN Antibody [NB100-58798] - Detection of Human SHARP by Western Blot of Immunoprecipitates. Samples: Whole cell lysate (1 mg for IP, 20% of IP loaded) from HeLa cells. Antibodies: Affinity purified rabbit anti-SHARP antibody... See more at [www.novusbio.com/NB100-58798](http://www.novusbio.com/NB100-58798)



Updated 3/9/2013 2.0

**Limitations:** This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit [www.novusbio.com/guarantee](http://www.novusbio.com/guarantee).**

**Novus USA**

8100 Southpark Way, A-8  
 Littleton, CO 80120  
 p) 888-506-6887  
 p) 303-730-1950  
 f) 303-730-1966  
[novus@novusbio.com](mailto:novus@novusbio.com)

**Novus Canada**

461 North Service Road West,  
 Unit B37  
 Oakville, ON L6M 2V5  
 p) 855-668-8722  
 f) 905-827-6402  
[canada@novusbio.com](mailto:canada@novusbio.com)

**Novus Europe**

12 Cambridge Science Park  
 Cambridge, UK CB4 0FQ  
 UK: p) +44-1223-426-001, f) +44-871-971-1635  
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79  
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340  
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31  
[europe@novusbio.com](mailto:europe@novusbio.com)

