9F, No. 108, Jhouzih St.,Taipei, Taiwan
Tel: + 886-2-8751-1888 Fax: + 886-2-6602-1218
E-mail: sales@abnova.com

Datasheet

HIP1R purified MaxPab mouse polyclonal antibody (B01P)

Catalog Number: H00009026-B01P

Regulation Status: For research use only (RUO)

Product Description: Mouse polyclonal antibody raised against a full-length human HIP1R protein.

Immunogen: HIP1R (NP_003950.1, 1 a.a. ~ 1068 a.a) full-length human protein.

Sequence:
MNSIKNVPARVLSRRPGHSLEAEREQFDKTQAISISKAI
NTQEAPVKEKHARRIILGTHHEKGAFTFWSYAIGLPLP
SSSILSWKFCHVLHKVLRDGHPNVLHDCQRYRSNIREI
GDLWGHLHDRYGQLVNVYTKLLLTKISFHLKHPQFPA
GLEVTDEVLEKAAGTDVNNIFQLTVEMFDYMDCELKLS
ESVFRQLNTAIAVSQMSSGQCRLAPLIQVIQDCSHLYH
YTVKLLFKLHSCLPADTLQGHRDRFHEQFHSLRNFFR
RASDMLYFKRLIQIPRLPEGPPNFLRASALAEHIKPVVV
IPEEAPEDEEPENLIEISTGPPAGEPVVVADLFDQTFGP
PNGSVKDDRDLQIESLKREVEMLRSELEKIKLEAQRYI
AQLKSQVNALEGELEEQRKQKQKALVDNEQLRHELA
QLRAAQLEGERSQGLREEAERKASATEARYNKLKEKH
SELVHVHAELLRKNADTAKQLTVTQQSQEEVARVKEQ
LAFQVEQVKRESELKLEEKSDQLEKLKRELEAKAGELA
RAQEALSHTEQSKSELSSRLDTLSAEKDALSGAVRQR
EADLLAAQSLVRETEAALSREQQRSSQEQGELQGRLA
ERESQEQGLRQRLLDEQFAVLRGAAAEAAGILQDAVS
KLDDPLHLRCTSSPDYLVSRAQEALDAVSTLEEGHAQ
YLTSLADASALVAALTRFSHLAADTIINGGATSHLAPTD
PADRLIDTCRECGARALELMGQLQDQQALRHMQASL
VRTPLQGILQLGQELKPKSLDVRQEELGAVVDKEMAA
TSAAIEDAVRRIEDMMNQARHASSGVKLEVNERILNSC
TDLMKAIRLLVTTSTSLQKEIVESGRGAATQQEFYAKN
SRWTEGLISASKAVGWGATQLVEAADKVVLHTGKYEE
LIVCSHEIAASTAQLVAASKVKANKHSPHLSRLQECSR
TVNERAANVVASTKSGQEQIEDRDTMDFSGLSLIKLKK
QEMETQVRVLELEKTLEAERMRLGELRKQHYVLAGAS
GSPGEEVAIRPSTAPRSVTTKKPPLAQKPSVAPRQDH
QLDKKDGIYPAQLVNY

Host: Mouse

Reactivity: Human,Mouse,Rat

Applications: IF, WB-Ce, WB-Tr
(See our web site product page for detailed applications information)

Protocols: See our web site at http://www.abnova.com/support/protocols.asp or product page for detailed protocols

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 9026

Gene Symbol: HIP1R

Gene Alias: FLJ14000, FLJ27022, HIP12, HIP3, ILWEQ, KIAA0655, MGC47513