

NEW! PRODUCT INTRODUCTION

PCR Plates

96 and 384-well, standard, half and full skirted



96-well for LightCycler[™] 100 µl




PRODUCT HIGHLIGHTS

Developed for use with the industry's most popular thermocyclers, Biotix PCR plates are manufactured and tested to ensure robust and reproducible amplification under the most exacting protocols. Made from medical-grade virgin polypropylene, these plates feature ultra-thin wall wells that provide excellent thermal transfer with PCR heat blocks. Each plate offers a molded-in alphanumeric grid to help with sample identification, and can withstand centrifugation up to 4,000 RCF when supported by the appropriate plate rotor adaptor. Slightly raised well rims facilitate secure sealing with films or strip caps. As with all Biotix products, PCR plates are free from heavy metals, mold releases or other extractables that could interfere with highly sensitive protocols. They are BioReady[™] Certified for purity.

| FEATURES | BENEFITS | |
|---|---|--|
| Ultra-clear, medical-grade virgin polypropylene | Biologically inert, offers excellent chemical and temperature resistance with superior clarity for sample visualization | |
| Ultra-thin walled construction | Ensures excellent thermal transfer with PCR heat blocks and uniform amplification | |
| Available in standard, half-skirt or full skirt | Broad range of compatibility with leading thermocycler brands; half and full-skir ed plates enable labeling on sides of plate | |
| BioReady™ Certified | PCR plates are certified free of RNase, DNase and endotoxins (pyrogens) | |

Product Dimensions



384-well Full Skirted 50 µl

Ordering Information

| Biotix Part No. | Description | Volume (Max. capacity/well) | Packaging |
|-----------------|---|-----------------------------|--------------------------------|
| P-0200-9C | PCR Plate, 96-well, Non-Skirted, Clear | 200µl | 10 plates/pack 5 packs/case |
| P-0200-9CHS | PCR Plate, 96-well, Half-Skirted, Clear | 200µl | 10 plates/pack 5 packs/case |
| P-0200-9CFS | PCR Plate, 96-well, Full-Skirted, Clear | 200µl | 10 plates/pack 5 packs/case |
| P-0100-9CHS | PCR Plate, 96-well, for LightCycler™, White | 100µl | 10 plates/pack 5 packs/case |
| P-0050-3CFS | PCR Plate, 384-well, Full-Skirted, Clear | 50µl | 10 plates/pack 5 packs/case |

©2013, Biotix, Inc. All rights reserved

Biotix, Fluid Innovation, Delta Filter, X-Resin, Blade, FlexFit, Statix, Leave Nothing Behind, BioReady, Tip Eject, and XTreme Quality are registered trademarks or trademarks of Biotix, Inc. All other brands and names contained herein are the property of their respective owners.

11/13

