

**NBP1-77722****Macrophage Inflammatory Protein 1 beta Antibody [Biotin]****Unit Size**

0.1 mg

**Concentration**

Please see the vial label for concentration.

**Storage**

Store at 4C. Do not freeze.

**Applications**

WB, ELISA

**Species**

Human

**Host**

Rabbit

**Clonality**

Polyclonal

**Conjugate**

Biotin

**Purity**

Delipidation and Defibrination

**Preservative**

0.01% Sodium Azide

**Immunogen**

This purified antibody was prepared from whole rabbit serum produced by repeated immunizations with full length recombinant human MIP-1beta protein.

**Recommended Dilutions**

ELISA 1:20000 - 1:100000, Western Blot 1:2000 - 1:10000

**Buffer**

0.02 M Potassium Phosphate, 0.15 M Sodium Chloride, pH 7.2 Stabilizer: 10 mg/ml Bovine Serum Albumin (BSA) - Immunoglobulin and Protease free

**Uses**

Human MIP-1 beta Antibody Biotin Conjugated has been tested for use in ELISA and western blotting. Expect a band approximately 15 kDa in size corresponding - human MIP-1Beta protein by western blotting in the appropriate cell lysate or extract. Immunology Research

**Images**This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: [www.novusbio.com/NBP1-77722](http://www.novusbio.com/NBP1-77722)

Updated 3/9/2013 2.0

*Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. For more information on our guarantee, please visit [www.novusbio.com/guarantee](http://www.novusbio.com/guarantee).*

**Novus USA**

8100 Southpark Way, A-8  
 Littleton, CO 80120  
 p) 888-506-6887  
 p) 303-730-1950  
 f) 303-730-1966  
[novus@novusbio.com](mailto:novus@novusbio.com)

**Novus Canada**

461 North Service Road West,  
 Unit B37  
 Oakville, ON L6M 2V5  
 p) 855-668-8722  
 f) 905-827-6402  
[canada@novusbio.com](mailto:canada@novusbio.com)

**Novus Europe**

12 Cambridge Science Park  
 Cambridge, UK CB4 0FQ  
 UK: p) +44-1223-426-001, f) +44-871-971-1635  
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79  
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340  
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31  
[europe@novusbio.com](mailto:europe@novusbio.com)

