MATERIAL SAFETY DATA SHEET

according to the Hazard Communication Standard (29 CFR 1910.1200)

Revision Date 07/19/2012 Version 1.1

SECTION 1. Identification

Product identifier

Product number	106580
Product name	di-Sodium hydrogen phosphate dihydrate for analysis EMSURE®

Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Reagent for analysis

Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation | 290 Concord Road, Billerica, MA 01821, United States of America | SDS Phone Support: +1-978-715-1335 | General Inquiries: +1-978-751-4321 | Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5) e-mail: mm_sds@merckgroup.com
Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week

SECTION 2. Hazards identification

GHS-Labeling

Not a hazardous substance or mixture according to Regulation (EC) No 1272/2008.

OSHA Hazards

While this material is not considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200), this MSDS contains valuable information critical to the safe handling and proper use of the product. This MSDS should be retained and available for employees and other users of this product.

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Formula	$Na_2HPO_4 * 2 H_2O$	$HNa_2O_4P * 2 H_2O$ (Hill)
CAS-No.	10028-24-7	
Molar mass	177.99 g/mol	

Remarks	No hazardous ingredients according to the OSHA Hazard Communication Standard 29CFR 19101200.

SECTION 4. First aid measures

Description of first-aid measures

Inhalation

After inhalation: fresh air.

Skin contact

After skin contact: wash off with plenty of water. Remove contaminated clothing.

Eye contact

After eye contact: rinse out with plenty of water with the eyelid held wide open. Call in ophthalmologist if necessary.

Ingestion

After swallowing: immediately make victim drink water (two glasses at most). Consult doctor in the event of any complaints.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

irritant effects

Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Not combustible.
Ambient fire may liberate hazardous vapors.
Fire may cause evolution of:
Oxides of phosphorus

Advice for firefighters

Special protective equipment for fire-fighters

In the event of fire, wear self-contained breathing apparatus.

Further information

Suppress (knock down) gases/vapors/mists with a water spray jet. Prevent fire extinguishing water from contaminating surface water or the ground water system.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Avoid inhalation of dusts. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions

Do not empty into drains.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.
Observe possible material restrictions (see sections 7 and 10).
Take up dry. Dispose of properly. Clean up affected area. Avoid generation of dusts.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Conditions for safe storage, including any incompatibilities

Tightly closed. Dry.

Store at +15°C to +25°C (+59°F to +77°F).

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Contains no substances with occupational exposure limit values.

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Change contaminated clothing. Wash hands after working with substance.

Eye/face protection

Safety glasses

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Recommended:

full contact:

Glove material:	Nitrile rubber
Glove thickness:	0.11 mm
Break through time:	> 480 min

splash contact:

Glove material:	Nitrile rubber
Glove thickness:	0.11 mm
Break through time:	> 480 min

Respiratory protection
required when dusts are generated.
Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state	solid
Color	off-white
Odor	odorless
Odor Threshold	not applicable
pH	9.0 - 9.4 at 50 g/l 68 °F (20 °C)
Melting point	198.5 °F (92.5 °C) Elimination of water of crystallization
Boiling point	No information available.
Flash point	does not flash
Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	not applicable
Upper explosion limit	not applicable
Vapor pressure	No information available.
Relative vapor density	No information available.
Relative density	2.1 g/cm³ at 68 °F (20 °C)
Water solubility	93 g/l at 68 °F (20 °C)

Partition coefficient: n-octanol/water	No information available.
Autoignition temperature	No information available.
Decomposition temperature	ca. 203 °F (95 °C)
Viscosity, dynamic	No information available.
Ignition temperature	not combustible
Bulk density	ca. 850 - 1,000 kg/m³

SECTION 10. Stability and reactivity

Reactivity
See below

Chemical stability
releases water of crystallization when heated.

Possibility of hazardous reactions
Exothermic reaction with:
Strong acids, antipyrine, acetates

Conditions to avoid
Strong heating.

Incompatible materials
no information available

Hazardous decomposition products
in the event of fire: See section 5.

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure
Eye contact, Skin contact, Ingestion

Acute oral toxicity
LD50 rat: > 2,000 mg/kg
OECD Test Guideline 401 (anhydrous substance)

Skin irritation
Possible damages:
After long-term exposure to the chemical: slight irritation

Eye irritation
Possible damages:
After long-term exposure to the chemical: slight irritation

Genotoxicity in vitro
Ames test
Result: negative
(anhydrous substance) (National Toxicology Program)

Specific target organ systemic toxicity - single exposure
The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure
The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard
Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC	No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
OSHA	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
ACGIH	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

Further information
Handle in accordance with good industrial hygiene and safety practice.

SECTION 12. Ecological information

Ecotoxicity

Toxicity to fish
LC50 Gambusia affinis (Mosquito fish): 467 mg/l; 48 h (anhydrous substance) (Lit.)

Toxicity to daphnia and other aquatic invertebrates
EC50 Daphnia magna (Water flea): 1,089 mg/l; 48 h (anhydrous substance) (Lit.)

Persistence and degradability
Biodegradability

The methods for determining the biological degradability are not applicable to inorganic substances.

Bioaccumulative potential
No information available.

Mobility in soil
No information available.

Other adverse effects

Additional ecological information
Discharge into the environment must be avoided.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)

Not classified as dangerous in the meaning of transport regulations.

Air transport (IATA)

Not classified as dangerous in the meaning of transport regulations.

Sea transport (IMDG)

Not classified as dangerous in the meaning of transport regulations.

SECTION 15. Regulatory information

United States of America

OSHA Hazards

No OSHA Hazards

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

SARA 311/312 Hazards

No SARA Hazards

Clean Water Act

The following Hazardous Substances are listed under the U.S. CleanWater Act, Section 311, Table 116.4A:
Ingredients
disodium hydrogen orthophosphate

The following Hazardous Chemicals are listed under the U.S. CleanWater Act, Section 311, Table 117.3:
Ingredients
disodium hydrogen orthophosphate

US State Regulations

Massachusetts Right To Know

Ingredients
disodium hydrogen orthophosphate

Pennsylvania Right To Know

Ingredients

disodium hydrogen orthophosphate
water of crystallization

New Jersey Right To Know

Ingredients
disodium hydrogen orthophosphate
water of crystallization

California Prop 65 Components

This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

Notification status

TSCA:	On TSCA Inventory
DSL:	All components of this product are on the Canadian DSL list.

SECTION 16. Other information

Training advice
Provide adequate information, instruction and training for operators.

Key or legend to abbreviations and acronyms used in the safety data sheet
Used abbreviations and acronyms can be looked up at www.wikipedia.org.

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.