



MATERIAL SAFETY DATA SHEET

according to the Hazard Communication Standard (29 CFR 1910.1200)

Revision Date 08/02/2012

Version 1.1

SECTION 1. Identification

Product identifier

Product number	107204
Product name	Certified sec. standard reference buffer solution potassium tetraoxalate dihydrate, directly traceable to primary SRM from NIST/PTB pH(S) = 1.68 ₁ (25°C) CertiPUR®

Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Reagent for analysis
-----------------	----------------------

Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation 290 Concord Road, Billerica, MA 01821, United States of America SDS Phone Support: +1-978-715-1335 General Inquiries: +1-978-751-4321 Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5) e-mail: mm_sds@merckgroup.com
---------	--

Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week
---------------------	--

SECTION 2. Hazards identification

GHS-Labeling

Hazard Statements

Not a dangerous substance according to GHS.

OSHA Hazards

While this material is not considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200), this MSDS contains valuable information critical to the safe handling and proper use of the product. This MSDS should be retained and available for employees and other users of this product.

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Chemical nature	Buffer solution
-----------------	-----------------

MATERIAL SAFETY DATA SHEET

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number	107204	Version 1.1
Product name	Certified sec. standard reference buffer solution potassium tetraoxalate dihydrate, directly traceable to primary SRM from NIST/PTB pH(S) = 1.68 ₁ (25°C) CertiPUR®	

Remarks	No hazardous ingredients according to the OSHA Hazard Communication Standard 29CFR 19101200.
---------	---

SECTION 4. First aid measures

Description of first-aid measures

Inhalation

After inhalation: fresh air.

Skin contact

After skin contact: wash off with plenty of water. Remove contaminated clothing.

Eye contact

After eye contact: rinse out with plenty of water.

Ingestion

After swallowing: make victim drink water (two glasses at most). Consult doctor if feeling unwell.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

The following applies to oxalates in general: nausea and vomiting after swallowing. Mucosal irritations, coughing, and dyspnoea after inhalation. Systemic effect: drop in the blood calcium level, toxic effect on kidneys, cardiovascular disorders.

Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Not combustible.

Ambient fire may liberate hazardous vapors.

Advice for firefighters

Special protective equipment for fire-fighters

In the event of fire, wear self-contained breathing apparatus.

Further information

none

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

MATERIAL SAFETY DATA SHEET

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number	107204	Version 1.1
Product name	Certified sec. standard reference buffer solution potassium tetraoxalate dihydrate, directly traceable to primary SRM from NIST/PTB pH(S) = 1.68 ₁ (25°C) CertiPUR®	

Advice for non-emergency personnel: Avoid substance contact. Do not breathe vapors, aerosols. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders:

Protective equipment see section 8.

Environmental precautions

No special precautionary measures necessary.

Methods and materials for containment and cleaning up

Observe possible material restrictions (see sections 7 and 10).

Take up with liquid-absorbent and neutralizing material (e.g. Chemisorb® H⁺, Merck Art. No. 101595). Dispose of properly. Clean up affected area.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Conditions for safe storage, including any incompatibilities

Tightly closed.

Storage temperature: no restrictions.

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Contains no substances with occupational exposure limit values.

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Change contaminated clothing. Application of skin- protective barrier cream recommended.
Wash hands after working with substance.

Eye/face protection

Safety glasses

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Recommended:

full contact:

Glove material:	natural latex
Glove thickness:	0.6 mm
Break through time:	> 480 min

MATERIAL SAFETY DATA SHEET

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number	107204	Version 1.1
Product name	Certified sec. standard reference buffer solution potassium tetraoxalate dihydrate, directly traceable to primary SRM from NIST/PTB pH(S) = 1.68 ₁ (25°C) CertiPUR®	

splash contact:

Glove material:	Nitrile rubber
Glove thickness:	0.11 mm
Break through time:	> 30 min

Other protective equipment:
protective clothing

Respiratory protection

required when vapors/aerosols are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state	liquid
Color	colorless
Odor	odorless
Odor Threshold	No information available.
pH	1.7 at 77 °F (25 °C)
Melting point	No information available.
Boiling point	No information available.
Flash point	No information available.
Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	No information available.
Upper explosion limit	No information available.
Vapor pressure	No information available.
Relative vapor density	No information available.
Relative density	1.003 g/cm ³ at 68 °F (20 °C)

MATERIAL SAFETY DATA SHEET

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number	107204	Version 1.1
Product name	Certified sec. standard reference buffer solution potassium tetraoxalate dihydrate, directly traceable to primary SRM from NIST/PTB pH(S) = 1.68 ₁ (25°C) CertiPUR®	

Water solubility	No information available.
Partition coefficient: n-octanol/water	No information available.
Autoignition temperature	No information available.
Decomposition temperature	No information available.
Viscosity, dynamic	No information available.

SECTION 10. Stability and reactivity

Reactivity

See below

Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

Possibility of hazardous reactions

are not to be expected because of low concentration of the dissolved substance(s); exception: substances undergoing a hazardous reaction with water.

Conditions to avoid

no information available

Incompatible materials

no information available

Hazardous decomposition products

no information available

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure

Eye contact, Skin contact

Acute oral toxicity

Acute toxicity estimate: > 2,000 mg/kg

Calculation method

Acute dermal toxicity

Acute toxicity estimate : > 2,000 mg/kg

Calculation method

Specific target organ systemic toxicity - single exposure

The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

MATERIAL SAFETY DATA SHEET

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number	107204	Version 1.1
Product name	Certified sec. standard reference buffer solution potassium tetraoxalate dihydrate, directly traceable to primary SRM from NIST/PTB pH(S) = 1.68 ₁ (25°C) CertiPUR®	

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC	No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
OSHA	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
ACGIH	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

Further information

Quantitative data on the toxicity of this product are not available.

Further toxicological data:

Other information

The following applies to oxalates in general: nausea and vomiting after swallowing. Mucosal irritations, coughing, and dyspnoea after inhalation. Systemic effect: drop in the blood calcium level, toxic effect on kidneys, cardiovascular disorders.

Further data:

Handle in accordance with good industrial hygiene and safety practice.

SECTION 12. Ecological information

Ecotoxicity

No information available.

Persistence and degradability

No information available.

Bioaccumulative potential

No information available.

Mobility in soil

No information available.

Other adverse effects

Additional ecological information

No ecological problems are to be expected when the product is handled and used with due care and attention.

MATERIAL SAFETY DATA SHEET

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number	107204	Version 1.1
Product name	Certified sec. standard reference buffer solution potassium tetraoxalate dihydrate, directly traceable to primary SRM from NIST/PTB pH(S) = 1.68 ₁ (25°C) CertiPUR®	

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)

Not classified as dangerous in the meaning of transport regulations.

Air transport (IATA)

Not classified as dangerous in the meaning of transport regulations.

Sea transport (IMDG)

Not classified as dangerous in the meaning of transport regulations.

SECTION 15. Regulatory information

United States of America

OSHA Hazards

No OSHA Hazards

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

SARA 311/312 Hazards

No SARA Hazards

US State Regulations

Massachusetts Right To Know

Remarks

No components are subject to the Massachusetts Right to Know Act.

Pennsylvania Right To Know

Ingredients

water

New Jersey Right To Know

Ingredients

water

potassium tetraoxalate

California Prop 65 Components

This product does not contain any chemicals known to the State of California to cause cancer,

MATERIAL SAFETY DATA SHEET
according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number	107204	Version 1.1
Product name	Certified sec. standard reference buffer solution potassium tetraoxalate dihydrate, directly traceable to primary SRM from NIST/PTB pH(S) = 1.68 ₁ (25°C) CertiPUR®	

birth, or any other reproductive defects.

Notification status

TSCA: On TSCA Inventory

DSL: This product contains one or several components listed in the
Canadian NDSL list.

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.