MATERIAL SAFETY DATA SHEET

according to the Hazard Communication Standard (29 CFR 1910.1200)

Revision Date 08/02/2012 Version 1.1

SECTION 1. Identification

Product identifier

Product number	109478
Product name	Ammonium buffer solution for complexometry (ammonium chloride/ammonia) pH = 10-11 TitriPUR®

Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Reagent for analysis

Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation | 290 Concord Road, Billerica, MA 01821, United States of America | SDS Phone Support: +1-978-715-1335 | General Inquiries: +1-978-751-4321 | Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5) e-mail: mm_sds@merckgroup.com
Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week

SECTION 2. Hazards identification

GHS Classification

Skin corrosion, Category 1B, H314
Specific target organ systemic toxicity - single exposure, Category 3, H335
Corrosive to Metals, Category 1, H290

For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word
Danger

Hazard Statements
H290 May be corrosive to metals.

H314 Causes severe skin burns and eye damage.
H335 May cause respiratory irritation.

Precautionary Statements
P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.
P301 + P330 + P331 IF SWALLOWED: rinse mouth. Do NOT induce vomiting.
P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P309 + P310 IF exposed or if you feel unwell: Immediately call a POISON CENTER or doctor/physician.

OSHA Hazards
This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

Other hazards
None known.

SECTION 3. Composition/information on ingredients

Chemical nature Ammonia solution

Hazardous ingredients
Chemical Name (Concentration)
CAS-No.
ammonia solution (>= 5 % - < 10 %)
1336-21-6
ammonium chloride (>= 5 % - < 10 %)
12125-02-9

SECTION 4. First aid measures

Description of first-aid measures

Inhalation
After inhalation: fresh air. Call in physician.

Skin contact
After skin contact: wash off with plenty of water. Immediately remove contaminated clothing. If available swab with polyethylene glycol 400. Call a physician immediately.

Eye contact
After eye contact: rinse out with plenty of water. Immediately call in ophthalmologist.

Ingestion
After swallowing: make victim drink water (two glasses at most), avoid vomiting (risk of perforation!). Call a physician immediately. Do not attempt to neutralize.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed
irritant effects, Cough, Shortness of breath, gastric pain, Unconsciousness, Bloody vomiting, Nausea, collapse, shock

Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Not combustible.

Ambient fire may liberate hazardous vapors.

Advice for firefighters

Special protective equipment for fire-fighters

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

Suppress (knock down) gases/vapors/mists with a water spray jet. Prevent fire extinguishing water from contaminating surface water or the ground water system.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Do not breathe vapors, aerosols. Avoid substance contact. Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders:

Protective equipment see section 8.

Environmental precautions

Do not let product enter drains.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills. Observe possible material restrictions (see sections 7 and 10). Take up with liquid-absorbent and neutralizing material (e.g. Chemizorb® OH^-, Merck Art. No. 101596). Dispose of properly. Clean up affected area.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Conditions for safe storage, including any incompatibilities

Tightly closed.

Store at +15°C to +25°C (+59°F to +77°F).

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Ingredients

Basis	Value	Threshold limits	Remarks
ammonia solution 1336-21-6			
ACGIH	Time Weighted Average (TWA):	25 ppm	
	Short Term Exposure Limit (STEL):	35 ppm	
NIOSH/GUIDE	Recommended exposure limit (REL):	25 ppm 18 mg/m³	
	Short Term Exposure Limit (STEL):	35 ppm 27 mg/m³	
OSHA_TRANS	PEL:	50 ppm 35 mg/m³	
Z1A	Short Term Exposure Limit (STEL):	35 ppm 27 mg/m³	
ammonium chloride 12125-02-9			
ACGIH	Time Weighted Average (TWA):	10 mg/m³	Form of exposure: Fume.
	Short Term Exposure Limit (STEL):	20 mg/m³	Form of exposure: Fume.
NIOSH/GUIDE	Recommended exposure limit (REL):	10 mg/m³	Form of exposure: Fume.
	Short Term Exposure Limit (STEL):	20 mg/m³	Form of exposure: Fume.
Z1A	Time Weighted Average (TWA):	10 mg/m³	Form of exposure: Fume.
	Short Term Exposure Limit (STEL):	20 mg/m³	Form of exposure: Fume.

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

Eye/face protection

Tightly fitting safety goggles

Hand protection
Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Recommended:

full contact:

Glove material:	Nitrile rubber
Glove thickness:	0.11 mm
Break through time:	> 480 min

splash contact:

Glove material:	natural latex
Glove thickness:	0.6 mm
Break through time:	> 30 min

Other protective equipment:
protective clothing

Respiratory protection
required when vapors/aerosols are generated.
Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state	liquid
Color	colorless
Odor	ammoniacal
Odor Threshold	No information available.
pH	10.5 at 68 °F (20 °C)
Melting point	No information available.
Boiling point	No information available.
Flash point	No information available.
Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	No information available.
Upper explosion limit	No information available.

Vapor pressure	No information available.
Relative vapor density	No information available.
Relative density	0.978 g/cm³ at 68 °F (20 °C)
Water solubility	at 68 °F (20 °C) soluble
Partition coefficient: n-octanol/water	No information available.
Autoignition temperature	No information available.
Decomposition temperature	No information available.
Viscosity, dynamic	No information available.

SECTION 10. Stability and reactivity

Reactivity
Explosible with air in a vaporous/gaseous state when heated.

Chemical stability
The product is chemically stable under standard ambient conditions (room temperature) .

Possibility of hazardous reactions
iodine, Strong acids, halogens

alkalines, Formed could be:

Ammonia

Conditions to avoid
no information available

Incompatible materials
Copper, various metals, metal alloys, Zinc

Hazardous decomposition products
in the event of fire: See section 5.

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure
Eye contact, Skin contact

Target Organs
Eyes
Skin
Respiratory system

Acute oral toxicity
Symptoms: Irritation of mucous membranes, Nausea, Bloody vomiting, Shortness of breath

Acute toxicity estimate: 26,667 mg/kg
Calculation method

Acute inhalation toxicity

Symptoms: Cough, Shortness of breath, mucosal irritations

Skin irritation
Irritations

Eye irritation
Irritations

Specific target organ systemic toxicity - single exposure
The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure
The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard
Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC	No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
OSHA	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
ACGIH	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

Further information
Quantitative data on the toxicity of this product are not available.
Further toxicological data:
After uptake:
gastric pain, shock, Unconsciousness, collapse
Further data:
Hazardous properties cannot be excluded.
Handle in accordance with good industrial hygiene and safety practice.

SECTION 12. Ecological information

Ecotoxicity

No information available.

Persistence and degradability

No information available.

Bioaccumulative potential

No information available.

Mobility in soil

No information available.

Other adverse effects

Additional ecological information

Biological effects:
Harmful effect due to pH shift.
Further information on ecology
Discharge into the environment must be avoided.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)

Not classified as dangerous in the meaning of transport regulations.

Air transport (IATA)

Not classified as dangerous in the meaning of transport regulations.

Sea transport (IMDG)

Not classified as dangerous in the meaning of transport regulations.

SECTION 15. Regulatory information

United States of America

OSHA Hazards

Target organ effects
Corrosive to skin
Corrosive to eyes
Respiratory irritant

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

SARA 311/312 Hazards

Acute Health Hazard
Chronic Health Hazard

US State Regulations

Massachusetts Right To Know

Ingredients
ammonia solution
ammonium chloride

Pennsylvania Right To Know

Ingredients
water
ammonia solution
ammonium chloride

New Jersey Right To Know

Ingredients
water
ammonia solution
ammonium chloride

California Prop 65 Components


This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

Notification status

TSCA:	On TSCA Inventory
DSL:	All components of this product are on the Canadian DSL list.

SECTION 16. Other information

National Fire Protection Association (U.S.A)



Training advice

Provide adequate information, instruction and training for operators.

Full text of H-Statements referred to under sections 2 and 3.

H290	May be corrosive to metals.
H314	Causes severe skin burns and eye damage.
H335	May cause respiratory irritation.

Key or legend to abbreviations and acronyms used in the safety data sheet
Used abbreviations and acronyms can be looked up at www.wikipedia.org.

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.