



MATERIAL SAFETY DATA SHEET

according to the Hazard Communication Standard (29 CFR 1910.1200)

Date of issue: 08/16/2012

Version 1.0

SECTION 1. Identification

Product identifier

Product number	109935
Product name	Potassium permanganate solution for 1000 ml, $c(\text{KMnO}_4) = 0.02 \text{ mol/l}$ (0.1 N) Titrisol®

Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Reagent for analysis
-----------------	----------------------

Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation 290 Concord Road, Billerica, MA 01821, United States of America SDS Phone Support: +1-978-715-1335 General Inquiries: +1-978-751-4321 Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5) e-mail: mm_sds@merckgroup.com
---------	--

Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week
---------------------	--

SECTION 2. Hazards identification

GHS Classification

Acute aquatic toxicity, Category 1, H400
Chronic aquatic toxicity, Category 1, H410

For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word
Warning

Hazard Statements

H410 Very toxic to aquatic life with long lasting effects.

MATERIAL SAFETY DATA SHEET

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number	109935	Version 1.0
Product name	Potassium permanganate solution for 1000 ml, $c(\text{KMnO}_4) = 0.02 \text{ mol/l}$ (0.1 N)	
	Titrisol®	

Precautionary Statements

P273 Avoid release to the environment.

OSHA Hazards

While this material is not considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200), this MSDS contains valuable information critical to the safe handling and proper use of the product. This MSDS should be retained and available for employees and other users of this product.

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Chemical nature	Aqueous solution
-----------------	------------------

Hazardous ingredients

Chemical Name (Concentration)

CAS-No.

Potassium permanganate ($\geq 5 \% - < 10 \%$)

7722-64-7

SECTION 4. First aid measures

Description of first-aid measures

Inhalation

After inhalation: fresh air.

Skin contact

After skin contact: wash off with plenty of water. Remove contaminated clothing.

Eye contact

After eye contact: rinse out with plenty of water with the eyelid held wide open. Call in ophthalmologist if necessary.

Ingestion

After swallowing: make victim drink water (two glasses at most). Consult doctor if feeling unwell.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

Vomiting, Stomach/intestinal disorders

Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

MATERIAL SAFETY DATA SHEET

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number	109935	Version 1.0
Product name	Potassium permanganate solution for 1000 ml, $c(\text{KMnO}_4) = 0.02 \text{ mol/l}$ (0.1 N) Titrisol®	

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Not combustible.

Ambient fire may liberate hazardous vapors.

Advice for firefighters

Special protective equipment for fire-fighters

In the event of fire, wear self-contained breathing apparatus.

Further information

Prevent fire extinguishing water from contaminating surface water or the ground water system.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Do not breathe vapors, aerosols. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions

Do not empty into drains.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7 and 10).

Take up with liquid-absorbent material (e.g. Chemisorb®). Dispose of properly. Clean up affected area.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Conditions for safe storage, including any incompatibilities

Tightly closed.

Store at +15°C to +25°C (+59°F to +77°F).

MATERIAL SAFETY DATA SHEET

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number	109935	Version 1.0
Product name	Potassium permanganate solution for 1000 ml, $c(\text{KMnO}_4) = 0.02 \text{ mol/l}$ (0.1 N)	
	Titrisol®	

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Ingredients

Basis	Value	Threshold limits	Remarks
<i>Potassium permanganate 7722-64-7</i>			
ACGIH	Time Weighted Average (TWA):	0.2 mg/m ³	Expressed as: as Mn
NIOSH/GUIDE	Recommended exposure limit (REL):	1 mg/m ³	Form of exposure: Fume. Expressed as: as Mn
	Short Term Exposure Limit (STEL):	3 mg/m ³	Form of exposure: Fume. Expressed as: as Mn
OSHA_TRANS	Ceiling Limit Value:	5 mg/m ³	Expressed as: as Mn
Z1A	Ceiling Limit Value:	5 mg/m ³	Expressed as: as Mn

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Change contaminated clothing. Wash hands after working with substance.

Eye/face protection

Safety glasses

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Recommended:

full contact:

Glove material:	Nitrile rubber
Glove thickness:	0.11 mm
Break through time:	> 480 min

splash contact:

Glove material:	Nitrile rubber
Glove thickness:	0.11 mm
Break through time:	> 480 min

Respiratory protection

required when vapors/aerosols are generated.

MATERIAL SAFETY DATA SHEET

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number	109935	Version 1.0
Product name	Potassium permanganate solution for 1000 ml, $c(\text{KMnO}_4) = 0.02 \text{ mol/l}$ (0.1 N)	
	Titrisol®	

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state	liquid
Color	blue
Odor	odorless
Odor Threshold	not applicable
pH	ca. 7.9 at 68 °F (20 °C)
Melting point	No information available.
Boiling point	No information available.
Flash point	No information available.
Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	No information available.
Upper explosion limit	No information available.
Vapor pressure	No information available.
Relative vapor density	No information available.
Relative density	1.03 g/cm ³ at 68 °F (20 °C)
Water solubility	at 68 °F (20 °C) soluble
Partition coefficient: n-octanol/water	No information available.
Autoignition temperature	No information available.
Decomposition temperature	No information available.
Viscosity, dynamic	No information available.

MATERIAL SAFETY DATA SHEET

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number	109935	Version 1.0
Product name	Potassium permanganate solution for 1000 ml, c(KMnO ₄) = 0.02 mol/l (0.1 N)	
	Titrisol®	

SECTION 10. Stability and reactivity

Reactivity

See below

Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

Possibility of hazardous reactions

The generally known reaction partners of water.

Conditions to avoid

no information available

Incompatible materials

no information available

Hazardous decomposition products

no information available

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure

Eye contact, Skin contact

Acute oral toxicity

Symptoms: After uptake of large quantities:, Vomiting, Stomach/intestinal disorders

Acute toxicity estimate: > 2,000 mg/kg

Calculation method

Specific target organ systemic toxicity - single exposure

The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC	No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
OSHA	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen

MATERIAL SAFETY DATA SHEET

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number	109935	Version 1.0
Product name	Potassium permanganate solution for 1000 ml, $c(\text{KMnO}_4) = 0.02 \text{ mol/l}$ (0.1 N) Titrisol®	

ACGIH by NTP.
No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

Further information

Quantitative data on the toxicity of this product are not available.

Other information

Manganese compounds are generally only very slightly absorbable via the gastrointestinal tract.

Further data:

Handle in accordance with good industrial hygiene and safety practice.

SECTION 12. Ecological information

Ecotoxicity

No information available.

Persistence and degradability

No information available.

Bioaccumulative potential

No information available.

Mobility in soil

No information available.

Other adverse effects

Additional ecological information

Biological effects:

Hazard for drinking water supplies.

Bactericidal effect.

Further information on ecology

Discharge into the environment must be avoided.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

MATERIAL SAFETY DATA SHEET

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number	109935	Version 1.0
Product name	Potassium permanganate solution for 1000 ml, $c(\text{KMnO}_4) = 0.02 \text{ mol/l}$ (0.1 N)	
	Titrisol®	

SECTION 14. Transport information

Land transport (DOT)

UN number	UN 3082
Proper shipping name	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (POTASSIUM PERMANGANATE)
Class	9
Packing group	III
Environmentally hazardous	--

Air transport (IATA)

UN number	UN 3082
Proper shipping name	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (POTASSIUM PERMANGANATE SOLUTION)
Class	9
Packing group	III
Environmentally hazardous	--
Special precautions for user	no

Sea transport (IMDG)

UN number	UN 3082
Proper shipping name	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (POTASSIUM PERMANGANATE SOLUTION)
Class	9
Packing group	III
Environmentally hazardous	--
Special precautions for user	yes
EmS	F-A S-F

MATERIAL SAFETY DATA SHEET

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number	109935	Version 1.0
Product name	Potassium permanganate solution for 1000 ml, $c(\text{KMnO}_4) = 0.02 \text{ mol/l}$ (0.1 N)	
	Titrisol®	

SECTION 15. Regulatory information

United States of America

OSHA Hazards

No OSHA Hazards

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

SARA 311/312 Hazards

No SARA Hazards

US State Regulations

Massachusetts Right To Know

Ingredients

Potassium permanganate

Pennsylvania Right To Know

Ingredients

water

Potassium permanganate

New Jersey Right To Know

Ingredients

water

Potassium permanganate

California Prop 65 Components

This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

Notification status

MATERIAL SAFETY DATA SHEET
according to the Hazard Communication Standard (29 CFR 1910.1200)


Product number	109935	Version 1.0
Product name	Potassium permanganate solution for 1000 ml, $c(\text{KMnO}_4) = 0.02 \text{ mol/l}$ (0.1 N) Titrisol®	

TSCA: On TSCA Inventory

DSL: All components of this product are on the Canadian DSL list.

SECTION 16. Other information

National Fire Protection Association (U.S.A)



Training advice

Provide adequate information, instruction and training for operators.

Full text of H-Statements referred to under sections 2 and 3.

H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.