

NBP1-92722**TNF Receptor I ELISA Kit [Biotin]****Unit Size**

96 Tests

Concentration

Concentration is not relevant for this product. Please see the protocols for proper use of this product.

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

ELISA

Species

Primate

Conjugate

Biotin

Immunogen

Sample Volume: 10 uL Suitable Sample Types: Cell culture supernatant, serum (baboon, cynomolgus) Sensitivity: 0.06 U/mL Standard Curve Range: 0.09 - 6.0 U/mL

Recommended Dilutions

ELISA

Uses

The monkey sTNF-R I ELISA is an enzyme-linked immunosorbent assay for the quantitative detection of monkey sTNF-R I

Images

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP1-92722

Notes

Components Included:

Aluminium pouch(es) with a Microwell Plate coated with monoclonal antibody to monkey sTNF-R I

HRP-Conjugate anti-monkey sTNF-R I monoclonal antibody

Monkey sTNF-R I Standard concentrate, 12 U/ml upon dilution

Assay Buffer Concentrate 20x (PBS with 1% Tween 20 and 10% BSA)

Wash Buffer Concentrate 20x (PBS with 1% Tween 20)

Substrate Solution (tetra... See more at www.novusbio.com/NBP1-92722

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

