

**NBP1-78048****TIP120B Antibody****Unit Size**

0.1 ml

**Concentration**

85 mg/ml

**Storage**

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

**Applications**

WB, ELISA, IHC, IHC-P

**Species**

Human

**Host**

Rabbit

**Clonality**

Polyclonal

**Purity**

Delipidation and Defibrination

**Preservative**

0.01% Sodium Azide

**Specificity/Sensitivity**

This product reacts with human, rat and mouse CAND2/TIP120B. Cross reactivity does occur with human, rat and mouse CAND1/TIP120A.

**Immunogen**

This antibody was prepared from whole rabbit serum produced by repeated immunizations with a synthetic peptide corresponding to amino acids 1130-1143 of Human CAND2/TIP120B (C-terminal) coupled to KLH.

**Recommended Dilutions**

ELISA 1:2000 - 1:10000, Immunohistochemistry, Immunohistochemistry-Paraffin, Western Blot 1:500 - 1:1000

**Buffer**

None Stabilizer: None

**Uses**

The antibody immunoprecipitates in vitro translated protein and protein from transfected cell lysates. Coimmunoprecipitation of related proteins has not been tested. A 125.4 kDa band corresponding - human CAND2 is detected. CAND2 is specifically expressed in muscle and heart tissue. Researchers should determine optimal titers for other applications.

**References (more available at [www.novusbio.com/NBP1-78048](http://www.novusbio.com/NBP1-78048))**

Waldman T, Kinzler KW, Vogelstein B. NEDD8 modification of CUL1 dissociates p120 (CAND1), an inhibitor of CUL1-SKP1 binding and SCF ligases. Mol Cell 2002 Dec [PMID: 12504025]

**Images**This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: [www.novusbio.com/NBP1-78048](http://www.novusbio.com/NBP1-78048)

Updated 3/9/2013 2.0

**Limitations:** This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit [www.novusbio.com/guarantee](http://www.novusbio.com/guarantee).**

**Novus USA**
 8100 Southpark Way, A-8  
 Littleton, CO 80120  
 p) 888-506-6887  
 p) 303-730-1950  
 f) 303-730-1966  
[novus@novusbio.com](mailto:novus@novusbio.com)
**Novus Canada**
 461 North Service Road West,  
 Unit B37  
 Oakville, ON L6M 2V5  
 p) 855-668-8722  
 f) 905-827-6402  
[canada@novusbio.com](mailto:canada@novusbio.com)
**Novus Europe**
 12 Cambridge Science Park  
 Cambridge, UK CB4 0FQ  
 UK: p) +44-1223-426-001, f) +44-871-971-1635  
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79  
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340  
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31  
[europe@novusbio.com](mailto:europe@novusbio.com)
