

NBP1-97911**Vimentin Antibody (RV202)****Unit Size**

1 ml

Concentration

This product is unpurified. The exact concentration of antibody is not quantifiable.

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

FLOW, IB, ICC/IF, IHC, IHC-Fr, IHC-P

Species

Human, Mouse, Rat, Canine, Chicken, Goat, Primate, Porcine, Zebrafish

Host

Mouse

Clonality

Monoclonal

Isotype

IgG1

Purity

Tissue culture supernatant

Preservative

0.09% Sodium Azide

Updated 3/9/2013 2.0

Specificity/Sensitivity

RV202 reacts exclusively with vimentin, which is expressed in mesenchymal cells and mesenchymal derived tumors e.g. lymphoma, sarcoma and melanoma.

Immunogen


RV202 is a mouse monoclonal IgG1 antibody derived by fusion of SP2/0-Ag14 mouse myeloma cells with spleen cells from a BALB/c mouse immunized with a cytoskeletal vimentin extract of calf lens.

Recommended Dilutions

Flow Cytometry, Immunoblotting, Immunocytochemistry/Immunofluorescence, Immunohistochemistry, Immunohistochemistry-Frozen, Immunohistochemistry-Paraffin

Images (more available at www.novusbio.com/NBP1-97911)

Immunocytochemistry/Immunofluorescence:
 Vimentin Antibody (RV202) [NBP1-97911] -
 Immunofluorescence staining of a 1 month old zebrafish embryo



Immunohistochemistry-Paraffin: Vimentin Antibody (RV202) [NBP1-97911] - Immunohistochemistry on paraffin section of human colon

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

