

NBP1-62178**MAP3K8 Antibody****Unit Size**

100 ug Reaction

Concentration

Please see the vial label for concentration.

Storage

Store at -20C. Avoid freeze-thaw cycles.

Applications

WB, ELISA

Species

Human, Mouse, Rat

Host

Rabbit

Clonality

Polyclonal

Purity

Affinity purified

Preservative

No Preservative

Specificity/Sensitivity

This antibody detects a single band of approximately 57kDa in PC-MAP3K8 samples

Immunogen

Synthetic peptides corresponding to unique epitope on MAP3K8. The peptide sequence was selected from C-terminal-region, amino acids 365-467. This peptide was covalently modified post-synthetically to achieve desired antigenicity.

Recommended Dilutions

ELISA < 1:10,000

Western Blot > 1:500

Buffer

0.62-0.65mg/ml in antibody stabilization buffer

Uses

By western blot this antibody detects a single band of approximately 57kDa in PC-MAP3K8 samples.

References (more available at www.novusbio.com/NBP1-62178)O'Neill LA. When signaling pathways collide: positive and negative regulation of toll-like receptor signal transduction. *Immunity*;29(1):12-20. 2008 Jul 18. [PMID: 18631453]**Images**This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP1-62178

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

