

NBP1-77806**MHC Class II Antibody****Unit Size**

0.1 ml

Concentration

90 mg/ml

Storage

Store at -20C. Avoid freeze-thaw cycles.

Applications

WB, ELISA

Species

Human

Host

Rabbit

Clonality

Polyclonal

Purity

Delipidation and Defibrination

Preservative

0.01% Sodium Azide

Immunogen

The immunogen used for this study was a bacterially produced recombinant FLAG-CIITA corresponding to amino acids 1 through 333 of the human protein.

Recommended Dilutions

ELISA 1:5000 - 1:25000, Western Blot 1:500 - 1:3000

Buffer

None Stabilizer: None

Uses

For immunoblotting a 1:500 dilution is recommended. Researchers should determine optimal titers for other applications.

Images

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP1-77806

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

