

NBP1-78057**Sumo 3 Antibody****Unit Size**

0.5 mg

Concentration

5 mg/ml

Storage

Store at 4C. Do not freeze.

Applications

WB, ELISA, ICC/IF

Species

Human

Host

Rabbit

Clonality

Polyclonal

Purity

Delipidation and Defibrination

Preservative

0.01% Sodium Azide

Immunogen

This purified antibody was prepared from rabbit serum after repeated immunizations with recombinant human SUMO-3 protein.

Recommended Dilutions

ELISA 1:4000 - 1:20000, Immunocytochemistry/Immunofluorescence, Western Blot 1:500 - 1:2000

Buffer

0.02 M Potassium Phosphate, 0.15 M Sodium Chloride, pH 7.2 Stabilizer: None

Uses

This purified polyclonal antibody reacts with human SuMO-3 by western blot and ELISA. Although not tested, this antibody is likely functional in immunohistochemistry and immunoprecipitation. This antibody using the specified conditions may recognize other prominent intrinsic bands. Other intrinsic bands are readily detectable at lower dilutions. Expect a band approximately 11.6 kDa in size corres... See more at www.novusbio.com/NBP1-78057

Images

Western Blot: Sumo 3 Antibody [NBP1-78057] - anti-Human SUMO-3 antibody to detect GFP-SUMO fusion proteins (arrowheads). Panel A. Increasing concentrations of human GFP-SUMO-3 were run on a SDS-PAGE, transferred onto nitrocellulose, and bloc... See more at www.novusbio.com/NBP1-78057



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

