

NBP1-76748**MTA2 Antibody****Unit Size**

0.1 mg

Concentration

1 mg/ml

Storage

Store at 4°C short term. Aliquot and store at -20°C long term. Avoid freeze-thaw cycles.

Applications

WB, ELISA, ICC/IF

Species

Human, Mouse, Rat

Host

Rabbit

Clonality

Polyclonal

Purity

Ion exchange chromatography

Preservative

0.02% Sodium Azide

Immunogen

Antibody was raised against a synthetic peptide corresponding to amino acids 652 to 668 of human PID (6), which differ from the mouse sequence by one amino acid.

Recommended Dilutions

ELISA, Immunocytochemistry/Immunofluorescence, Western Blot

Buffer


PBS containing 0.02% sodium azide.

Uses

PID antibody can be used for detection of PID by Western blot at 0.5 to 1 mg/ml. HeLa cell lysate can be used as positive control and a 75 kDa band can be detected. It is human, mouse, and rat reactive and has no cross response to MTA1.

Images

Western Blot: MTA2 Antibody [NBP1-76748] - HeLa whole cell lysates in the absence (A) or presence (B) of blocking peptide with MTA2 antibody at 1 ug/ml.



Immunocytochemistry/Immunofluorescence: MTA2 Antibody [NBP1-76748] - HeLa using MTA2 antibody at 10 ug/ml.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA
 8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com
Novus Canada
 461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com
Novus Europe
 12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com
