

NBP1-46356**BASP1 Antibody****Unit Size**

0.1 ml

Concentration

lyoph

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

WB, IHC, IHC-Fr, IHC-P

Species

Mouse, Rat

Host

Rabbit

Clonality

Polyclonal

Purity

Whole antisera

Preservative

No Preservative

Specificity/Sensitivity

Specific for BASP1.

Immunogen

A synthetic peptide from n-terminal region of mouse Brain acid soluble protein 1 (BASP1) conjugated to an immunogenic carrier protein was used as the antigen.

Recommended Dilutions

Immunohistochemistry-Frozen, Western Blot 1:300-1:2000, Immunohistochemistry-Paraffin, Immunohistochemistry

Buffer

lyophilized: Reconstitute in 100 µl of sterile water. Centrifuge to remove any insoluble material.

Uses

Immunohistochemistry-Paraffin/Frozen, Western Blot. A dilution of 1 : 300 to 1 : 2000 is recommended. The optimal dilution should be determined by the end user. Not yet tested in other applications.

ImagesThis product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP1-46356

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. For more information on our guarantee, please visit www.novusbio.com/guarantee.

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

