
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-33309

NBP1-33309

SUG1 Antibody



Unit Size
0.1 mg

Concentration
Concentrations vary lot to lot. See vial label for concentration.

Storage
Store at -20C. Avoid freeze-thaw cycles.

Applications
WB, ICC/IF, IHC, IHC-P

Species
Human

Host
Rabbit

Clonality
Polyclonal

Purity
Affinity purified

Preservative
0.01% Thimerosal

Updated 3/9/2013 2.0

Immunogen
Recombinant protein fragment contain a sequence corresponding to a region within amino acids 66 and 377 (P62195) of PSMC5


Recommended Dilutions
Immunocytochemistry/Immunofluorescence, Immunohistochemistry, Immunohistochemistry-Paraffin, Western Blot 1:500-1:3000

Buffer
0.1M Tris, 0.1M Glycine, 10% Glycerol (pH7.0).

Uses
Western blot. The usefulness of this product in other applications has not been determined.

Images (more available at www.novusbio.com/NBP1-33309)

Western Blot: SUG1 Antibody [NBP1-33309] - Sample (30 ug of whole cell lysate) A: A431 B: Hep G2 10% SDS PAGE; antibody diluted at 1:1000.



Immunocytochemistry/Immunofluorescence: SUG1 Antibody [NBP1-33309] - Paraformaldehyde-fixed A549, using antibody at 1:200 dilution.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com