
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-59732

NBP1-59732

SLC1A5 Antibody



Unit Size
0.1 mg

Concentration
lyoph

Storage
Store at -20C. Avoid freeze-thaw cycles.

Applications
WB, IHC, IHC-P

Species
Human, Mouse, Rat, Bovine, Canine, Chicken, Rabbit, Xenopus, Zebrafish

Molecular Weight
57kDa

Host
Rabbit

Clonality
Polyclonal

Purity
Protein A purified

Preservative
No Preservative

Updated 3/9/2013 2.0

Immunogen
Synthetic peptides corresponding to SLC1A5(solute carrier family 1 (neutral amino acid transporter), member 5) The peptide sequence was selected from the middle region of SLC1A5 (NP_005619). Peptide sequence FGVALRKLGPEGELLIRFFNSFNEATMVLVSWIMWYAPVGIMF

Recommended Dilutions
Immunohistochemistry 4-8 ug/ml, Immunohistochemistry-Paraffin 4-8 ug/ml, Western Blot 2.5 ug/ml

Buffer
Lyophilized from PBS. Reconstitute in 100 ul distilled water to a final antibody concentration of 1 mg/ml.

Images

Western Blot: SLC1A5 Antibody [NBP1-59732] - Jurkat cell lysate, Antibody Titration: 2.5ug/ml

Immunohistochemistry-Paraffin: SLC1A5 Antibody [NBP1-59732] - Human kidney Tissue, antibody concentration 4-8ug/ml. Cells with positive label: renal corpuscle cells (indicated with arrows) 400X magnification.

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com