

NBP1-32959**Tubulin alpha-1B Antibody****Unit Size**

0.1 ml

Concentration

Concentrations vary lot to lot. See vial label for concentration.

Storage

Store at -20C. Avoid freeze-thaw cycles.

Applications

WB, ICC/IF, IHC-P

Species

Human

Host

Rabbit

Clonality

Polyclonal

Purity

Affinity purified

Preservative

0.01% Thimerosal

Marker

Microtubule Marker

Immunogen

Recombinant protein fragment contain a sequence corresponding to a region within amino acids 118 and 365 (P68363) of alpha Tubulin

Recommended Dilutions

Immunocytochemistry/Immunofluorescence, Immunohistochemistry-Paraffin, Western Blot 1:500-1:3000

Buffer


0.1M Tris, 0.1M Glycine, 10% Glycerol (pH7.0).

Uses


Western blot. The usefulness of this product in other applications has not been determined.

Images (more available at www.novusbio.com/NBP1-32959)

Western Blot: Tubulin alpha-1B Antibody [NBP1-32959] - Sample (30 ug of whole cell lysate) A: HeLa 10% SDS PAGE; antibody diluted at 1:1000.



Immunocytochemistry/Immunofluorescence: Tubulin alpha-1B Antibody [NBP1-32959] - Analysis of Tubulin alpha-1B chain on A431, using NBP1-32959.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

